

Roverpet #F24W6 2'x4' Wheeled Floor Assembly Instructions



Inventory List for The Roverpet #F24W6 2' x 4' Wheeled PVC Floor:

- (1) #F24W6 Wheeled PVC Floor for 2'x4' pet cage **AND/OR**
- (2) #F24W6 Drilled PVC Floor for 4'x4' pet crate
- (3) #LC Locking Swivel Casters for each included floor
- (3) #NLC Non-locking Swivel Casters for each included floor
- (6) #CWC Caster Wheel Clips for each included floor
- (12) #250 Floor Clips for each included floor

Assembly Procedure

- 1.) Unpack contents of shipping carton and compare to inventory list above.
- 2.) Place the #F24W6 floor, flat side down, on your floor.
- 3.) Decide where will be the easiest access points to access the (3) #LC Locking Castors for your desired location for the unit.
- 4.) From the bottom side of the #F24W6 floor, insert the shaft of locking castors into the locations decided on in the prior step. Make certain the castor's base is resting completely on the floor.



- 5.) Install the #CWC Castor Wheel Clips into the locking channel located just above the floor frame, near the top of each castor shaft. Push the #CWC Castor Wheel Clip firmly into the channel, locking the shaft into position.



- 6.) Install the remaining **(3) #NLC Non-locking Castors** into the remaining three castor holes using the same process used for the Locking Castors.
- 7.) Place your existing Roverpet dog cage/unit over the #F24W6 floor.
- 8.) The Roverpet dog cage will rest on the outside of the #F24W6 floor frame.




- 9.) With the Roverpet pet cage positioned over the #F24W6 floor, install **(2) #250 floor clips** for each PVC panel. Snap the clip over the panel frame and #F24W6 floor frame, securing the panel to the #F24W6 floor.



Note: If your pet cage contains a door panel, place the **(2) #250** clips just to the inside of the door opening area.



- 10.) For multi-floor pet crates: Install **(4) #250 floor clips** over the #F24W6 floor frames where they meet together. Place **(2) #250 floor clip** at the furthest most points of the #F24W6 frames and **(2) more #250 floor clips** evenly spaced across the two #F24W6 floor frames. Connecting the pet enclosure panels to the #F24W6 floor frames involves the same process as step #8.



Congratulations, you are now ready to use your Roverpet Dpg Cage with Wheeled Floor!

Special Notes:

40 lbs. maximum weight allowed on **each** of the Roverpet #F24W6 Wheeled Floor at any one time.

For multi-units or PVC panels taller than 36", additional #250 Floor Clips will be required (not included).

Please contact Roverpet for assistance with your particular needs.

CAUTION

*** ONCE THE FLOORS ARE ASSEMBLED **DO NOT** WALK ON THEM ***

Property of Roverpet

www.roverpet.com

